

DLCLB-SM-HC3

HELIAX®, LC Loopback, Single mode, blue



OBSOLETE

This product was discontinued on: July 29, 2020

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber loopback
Product Brand	HELIAX®

General Specifications

Interface	LC/UPC
------------------	--------

Material Specifications

Ferrule Material	Zirconia
-------------------------	----------

Mechanical Specifications

Mating Durability, maximum	0.5 dB @ 500 cycles
-----------------------------------	---------------------

Optical Specifications

Insertion Loss, maximum	1 dB
--------------------------------	------

Environmental Specifications

Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

DLCLB-SM-HC3

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

