

C400-HMHM

Base Product



CNT-400 CNT® Jumper with interface types 4.3-10 Male and 4.3-10 Male, variable length

Product Classification

| | |
|-----------------------|------------------------|
| Product Type | Braided cable assembly |
| Product Brand | CNT® |
| Product Series | CNT-400 |

General Specifications

| | |
|---|---|
| Attachment, Connector A | Factory attached |
| Attachment, Connector B | Factory attached |
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Cable Family | CNT-400 |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | A |
| Variable Length | For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative |

Dimensions

| | |
|---------------------|------------|
| Length | 0 m 0 ft |
| Nominal Size | 0.400 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 700–3000 MHz | 1.433 | 14.99 |

Jumper Assembly Sample Label

C400-HMHM



Included Products

- 400PHM-C-CR – Type 4.3-10 Male connector for CNT-400 braided cable
- CNT-400 – CNT-400, CNT[®] 50 Ohm Braided Coaxial Cable, variable, black PE jacket