

M81C Coaxial Coupler, Electrical Ivory

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Multimedia coupler
Product Series	SL Series
Warranty	For more information, please consult our Product Warranty guidelines

General Specifications

Application	Module designed for video applications
Color	Electrical ivory
Interface Type	Speaker post
Mounting	Snap-in
Outlet Orientation	Flat
Total Ports, quantity	1

Dimensions

Height	20.574 mm 0.81 in
Width	14.478 mm 0.57 in
Depth	16.002 mm 0.63 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

*** Footnotes****Warranty**

For more information, please consult our Product Warranty guidelines