

PFP-PX-S2



Power Express Class 2 shelf, accommodates up to 2 modules of 8 SELV /Class 2 outputs, 1U

- Integrated chassis control and management with immediate detection of active module alarms

Power Express Class 2 shelf for up to 16 NEC Class 2 circuits. Alarm card, Controller card and power modules sold separately

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Power supply subrack
Warranty	One year

General Specifications

Color	White
Rack Type	19 in
Rack Units	1
Shelf Movement	Fixed

Dimensions

Height	44.45 mm 1.75 in
Width	444.5 mm 17.5 in
Depth	285.75 mm 11.25 in

Electrical Specifications

Input Voltage Range	100 to 240 Vac
Electrical Safety Standard	CSA C22.2 No. 60950-1-03 IEC 60950-1 UL
Total Output Power	1600 W

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–95%, non-condensing
Standards Compliance	EN 61000-4-2 level 4 GR 1089, Issue 4

PFP-PX-S2

Packaging and Weights

Packaging quantity	1
Packaging Type	Carton
Weight, net	2.948 kg 6.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
-----------------	--