

F4C-NMNM-10M-E1

HELIAX® 1/2" Superflexible SureFlex® Jumper with interface types N Male and N Male, 10M



Product Classification

| | |
|-----------------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|-------------------------------------------|----------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|------------------|
| Length | 10 m 32.808 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|-----------------------------------------|----------------------|
| 3rd Order IMD Static | -112 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz | 1.065 | 30 |
| 1700–2200 MHz | 1.065 | 30 |
| 2200–2700 MHz | 1.106 | 26 |

F4C-NMNM-10M-E1

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition