ALGLUUCCF

Base Product



Ultra Low Loss Method A Singlemode LC/UPC Uniboot to
Unconnectorized Ruggedized Fanout Cable, 24-Fiber, Plenum, 250µm 12
fiber PmP

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

 Product Type
 Ruggedized fanout

 Product Brand
 SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A Blue

Color, connector A Blue

Construction Type Stranded

 Interface, Connector A
 LC/UPC

 Interface Feature, connector A
 Uniboot

Jacket Color Red

Polarity Method A

Fibers per Subunit, quantity 12

Total Fibers, quantity 24

Dimensions


Cable Assembly Length Range (m) 3 – 999

Cable Assembly Length Range (ft) 8 – 999

Ordering Tree



ALGLUUCCF



Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance Dca

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

COMMSCOPE®

ALGLUUCCF

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

760259927 P-024-MP-8G1P-F12RD/20T

860658160 – LC/UPC Uniboot Connector, Singlemode, Blue

Fiber indoor cable, Plenum for MPO Trunks, 24 fiber with 12 fiber subunits, Prysmian BBXS Singlemode G.657.A2/B2, Feet jacket marking, Red jacket color, Light Duty

