## 1509891-003 | RLS12-3B-15A



### REGAL RLS 1.2 GHz RF splitter, 3 balanced outputs, AC power#passing

 \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

- Support DOCSIS® 3.1 expanded bandwidth up to 1218 MHz
- Maintain existing Regal installed base with compatible faceplate upgrades
- Easily configured to enable or block AC power as needed in the network
- Faceplate only options for cost-effective upgrades to existing Regal deployments
- Support aerial or pedestal installation with flexible design
- Protect valuable network equipment investment with heavy surge suppression options available

#### Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Splitter
Product Series REGAL

Government Funding Build America Buy America (BABA) compliant\*

## General Specifications

**Location of Manufacturing**Waived per BABA waiver for BEAD Program

#### Dimensions

 Height
 116.84 mm | 4.6 in

 Depth
 76.2 mm | 3 in

 Length
 139.7 mm | 5.5 in

## **Electrical Specifications**

Current Handling, ac ports 20 A

Current Handling, RF ports 15 A

**Operating Frequency Band** 5 – 1218 MHz

Surge Protection No

## **Environmental Specifications**



# 1509891-003 | RLS12-3B-15A

**Operating Temperature** 

-40 °C to +60 °C (-40 °F to +140 °F)

Packaging and Weights

**Weight** 0.68 kg | 1.5 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

