



IFDB Fiber Optic Wall Box with 8 SC/APC adapters, 1 preterminated 1x8 splitter

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

## Product Classification

Regional Availability	EMEA
Product Type	Fiber wall box
Product Series	IFDB

## General Specifications

Functionality	Patching   Splitting
Adapters, quantity	8
Color	Light gray
Front Cover Type	Screw-on
Interface	SC/APC
Mounting	Floor   Wall

## Dimensions

Height	216 mm   8.504 in
Width	126 mm   4.961 in
Depth	49 mm   1.929 in

## Material Specifications

Material Type	Thermoplastic
---------------	---------------

## Optical Specifications

Fiber Mode	Singlemode
------------	------------

## Environmental Specifications

# 760242273 | IFDB-M-T-A08S2-118-1

Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP30

## Packaging and Weights

Included	Optical splitter (1)
Packaging quantity	12
Packaging Type	Bag   Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

