


# CS3813-000 | FIST-OC-GA41200L2-LS



FIST GPST fiber patch/splitter tray, four 1x2 splitters, FBT, symmetrical split ratio, LC/APC, gray, left oriented

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Splitter patch tray
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-OC-G

## General Specifications

<b>Device Type</b>	FIST patch tray
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Fused biconic tapered
<b>Application</b>	For use with FIST panels
<b>Circuits, quantity</b>	4
<b>Distribution Type</b>	1 x 2 splitter
<b>Interface, front</b>	LC/APC
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Module Color</b>	Gray
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	4
<b>Tray Orientation</b>	Left orientation

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value

# CS3813-000 | FIST-OC-GA41200L2-LS

---

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant

