


CZ5627-000 | FIST-GPSTF-12-QAN-2



FIST GPST Fiber Termination/Splice Tray, 12/24 ports, no adapters, ANT splice chip, 15 in, gray, left patch cord routing

Product Classification

Regional Availability	EMEA
Product Type	Fiber patch/splice tray
Product Brand	FIST®
Product Series	FIST-GPST

General Specifications

Functionality	Patching Splicing
Color	Gray
Interface, front	Unloaded
Patch Cord Entry Location	Front, left side
Splicing Type	ANT, single fiber fusion
Total Ports, quantity	12

Dimensions

Height	16 mm 0.63 in
Width	315 mm 12.402 in
Depth	190 mm 7.48 in

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

CZ5627-000 | FIST-GPSTF-12-QAN-2

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

