FDC-AT-S28-02018



FDC Fiber Optic Splice/Patch Closure, Gel Cable Sealing, 8 SC/APC Adapters, 24 fusion splices

Product Classification

Regional AvailabilityAsia | EMEA | Latin AmericaProduct TypeIn-line, rectangular fiber closure

Product Series FDC

General Specifications

Cable Ports Quantity, total6 round portsCable Sealing TypeCompressed gelClosure Sealing TypeHinged with latch

Closure Style In-line
Color Black

Mounting Manhole | Pedestal | Strand | Wall

Port Type SC/APC

Port, quantity 8

Splice Tray Included, quantity 1

Splice Tray Type Included 24-way, heat shrink

Splitter Type No splitter

Splitter, quantity 0

Dimensions

 Height
 83 mm | 3.268 in

 Width
 160 mm | 6.299 in

 Length
 270 mm | 10.63 in

Material Specifications



FDC-AT-S28-02018

Material Type

Rugged polymer

Environmental Specifications

Environmental Space Above ground | Below ground

Packaging and Weights

Included Splitter (1)

Packaging quantity

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant





