

LSX-675063-A-SPL



LSX Fiber Termination/Splice Panel 4 Ru, 72 - SC/UPC, Singlemode Stranded

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	LSX

General Specifications

Functionality	Patching Splicing
Application	Used in LSX-style frames only
Cable Stub Type	Pigtails, stranded
Color	Putty white
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Interface, rear	Stub tail
Rack Type	EIA 19 in EIA 23 in
Rack Units	4
Shelf Movement	Fixed
Splicing Type	Mechanical, mass fusion
Total Ports, quantity	72

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	381 mm 15 in

Material Specifications

Finish	Powder coated
Material Type	Steel

LSX-675063-A-SPL

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

