


354214-000 | FIST-GSS2-KIT03-A



FIST-GSS2 Fiber Splice Panel, 3RU, 19 in, for splicing loose tube cable to pigtail, Single circuit trays included, for ANT splice protector, gray

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Brand	FIST®
Product Series	FIST-GSS2

General Specifications

Functionality	Splicing
Application	Compatible with FIST-GR3-style frames
Cable Exit Location	Rear, right side
Cable Stub Type	Indoor/outdoor, stranded
Color	Gray
Interface, front	Unloaded
Rack Type	EIA 19 in ETSI 600 mm FIST-GR3
Rack Units	3
Shelf Movement	Sliding
Splice Trays Included, quantity	48
Splicing Capacity, maximum	96
Splicing Type	ANT, single fiber fusion

Dimensions

Height	133.35 mm 5.25 in
Width	482.6 mm 19 in

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

