61935G-000 | OCM5-SP11W00S2-20DASIA



OCM5 Fiber Optic Splitter Module, Planar, one 1x32 Splitter, singlemode, sC/APC, symmetrical split ratio, 2.0 m pigtails

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

Product Series OCM5

General Specifications

Device Type Standard VAM

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Access Front

Application For use with FIST cabinets

Circuits, quantity

Distribution Type 1 x 32 splitter

Interface, InputSC/APCInterface, OutputSC/APC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

 Height
 154 mm | 6.063 in

 Width
 16 mm | 0.63 in

 Depth
 142 mm | 5.591 in

 Pigtail Length, Input
 2 m | 6.562 ft

Pigtail Length, Output 2 m | 6.562 ft

Packaging and Weights



61935G-000 | OCM5-SP11W00S2-20DASIA

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

