



ReadyPATCH® Multimode OM4 Keyed Module, 12 LC ports, blue

- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	LazrSPEED® ReadyPATCH®

General Specifications

Functionality	Breakout
Adapters, quantity, front	6
Adapters, quantity, rear	1
Color, front	Blue
Color, rear	Gray
Interface, front	LC/UPC
Interface Feature, front	Keyed
Interface, rear	MPO
Interface Feature, rear	Male
Polarity	Method B
Shuttered	Yes
Total Fibers, quantity	12
Total Ports, quantity, front	12

Dimensions

Height	27.94 mm 1.1 in
Width	129.54 mm 5.1 in
Depth	127 mm 5 in

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Fiber Type	OM4, LazrSPEED® 550
Insertion Loss Change, mating	0.3 dB
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.9 dB

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant



Included Products

460117393	- LazrSPEED® LC Duplex Hybrid Keyed Adapter, Blue
-----------	---------------------------------------------------

* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

460117393

LazrSPEED® LC Duplex Hybrid Keyed Adapter, Blue

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	LazrSPEED®

General Specifications

Body Style	Duplex
Color	Blue
Interface	LC/UPC
Interface Feature	Keyed
Mounting	No flange
Shuttered	No
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Multimode Singlemode
-------------------	------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

