



## ReadyPATCH® Singlemode Keyed Module, 12 LC ports, brown

- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	ReadyPATCH®   TeraSPEED®

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, front</b>	6
<b>Adapters, quantity, rear</b>	1
<b>Color, front</b>	Brown
<b>Color, rear</b>	Gray
<b>Interface, front</b>	LC/UPC
<b>Interface Feature, front</b>	Keyed
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Male
<b>Polarity</b>	Method B
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	12
<b>Total Ports, quantity, front</b>	12

## Dimensions

<b>Height</b>	27.94 mm   1.1 in
<b>Width</b>	129.54 mm   5.1 in
<b>Depth</b>	127 mm   5 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

# 760087957 | RFE-MOD-012-8W-MPO-LC02-KBR

---

<b>Fiber Type</b>	G.652.D and G.657.A1, TeraSPEED®   OS2
<b>Insertion Loss Change, mating</b>	0.3 dB
<b>Insertion Loss Change, temperature</b>	0.3 dB
<b>Insertion Loss, maximum</b>	1.15 dB

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

460117450	– LazrSPEED® LC Duplex Hybrid Keyed Adapter, Brown
-----------	--

## \* Footnotes

<b>Insertion Loss Change, mating</b>	Maximum insertion loss change after 500 matings
<b>Insertion Loss Change, temperature</b>	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)