

760231506 | HD-1U-SP



High Density 1U Sliding fiber Splice Panel, accepts (4) G2 modules, providing up to 48 duplex LC ports, accepts splice wallets, RoloSplice trays and stackable splice trays

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	HD

General Specifications

Color	Black Gray
Intelligence Type	iPatch® ready
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding

Dimensions

Height	44.45 mm 1.75 in
Width	450.85 mm 17.75 in
Depth	505.46 mm 19.9 in

Material Specifications

Material Type	Steel
----------------------	-------

Environmental Specifications

Safety Standard	UL 1863
------------------------	---------

Packaging and Weights

Packaging quantity	1
Weight, net	5.375 kg 11.85 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

