

760231522 | HD-4U-SP



High Density 4U Sliding Fiber Splice Panel, to accommodate a maximum of 192 single fusion splices when using the Splice Wallet® or 128 single fusion splices when using the RoloSplice® splice tray organizers

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	HD

General Specifications

Color	Black Gray
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	4
Shelf Movement	Sliding

Dimensions

Height	177.8 mm 7 in
Width	450.85 mm 17.75 in
Depth	406.4 mm 16 in

Material Specifications

Material Type	Steel
----------------------	-------

Environmental Specifications

Safety Standard	UL 1863
------------------------	---------

Packaging and Weights

Packaging quantity	1
Weight, net	5.216 kg 11.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

