

# 760237333 | HD-iP-4U-384F-LC-DM-TS-FX

HD iPATCH 4U 384F-LC Distribution Module, TeraSPEED, Fixed Shelf



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Brand</b>	iPatch®   imVision®
<b>Product Series</b>	HD

## General Specifications

<b>Color</b>	Black   Gray
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, front</b>	LC/UPC
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	192

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	553.97 mm   21.81 in

## Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
RCM	Compliant to electrical safety & telecommunications requirements
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

