

760118331 | M2400A-1U-PS



M2400 1U Angled Modular Panel, 24 port (MPS100 / UNJ10G / UNJ600 / UNJ600T / UNJ500), Black

OBSOLETE

This product was discontinued on: January 31, 2025

Replaced By:

760118349
M2400A-1U-GS

M2400 1U Angled Modular Panel, 24 port (MGS600 / MGS400 / MPS100 / UNJ10GT / UNJ600T / UNJ10G / UNJ600 / UNJ500), Black

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

RJ45 patch panel

Product Series

M Series

General Specifications

ANSI/TIA Category

5e | 6

Cable Type

Unshielded

Color

Black

Intelligence Type

Passive

Panel Style

Angled

Rack Type

EIA 19 in

Rack Units

1

Total Ports, quantity

24

Dimensions

Height

43.69 mm | 1.72 in

Width

482.6 mm | 19 in

Depth

138.18 mm | 5.44 in

Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

760118331 | M2400A-1U-PS

Compatible Diameter Over Dielectric, minimum 0.762 mm | 0.03 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-coated steel

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

