



SYSTIMAX 360™ iPatch® Upgrade Kit for Evolve Angled Panel, 48 Port, 5 pack

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

SYSTIMAX®

### Product Type

RJ45 patch panel

### Product Brand

SYSTIMAX 360™ | iPatch®

## General Specifications

### ANSI/TIA Category

6 | 6A

### Color

Cool gray

### Intelligence Type

iPatch® upgrade kit

### Panel Style

Angled

### Total Ports, quantity

48

## Dimensions

### Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

### Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

## Electrical Specifications

### Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

### Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

### Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

## Material Specifications

### Material Type

Acrylonitrile butadiene styrene (ABS) | Polycarbonate

## Environmental Specifications

### Operating Temperature

-5 °C to +50 °C (+23 °F to +122 °F)

### Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

# 760202648 | 360-iP-UP-KIT-AE-48

---

<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	ACMA   CE   UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	5
<b>Weight, net</b>	0.113 kg   0.25 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

