

# 760220418 | 360CM12-4x6-TS

---

G2 4x6 Singlemode Conversion Module, 6 MPO male ports



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, front</b>	6
<b>Adapters, quantity, rear</b>	4
<b>Color, front</b>	Blue
<b>Color, housing</b>	Black
<b>Color, rear</b>	Blue
<b>Data Module Type</b>	Standard
<b>Interface, front</b>	MPO
<b>Interface Feature, front</b>	Standard
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Male   Reduced footprint
<b>Polarity</b>	Method B
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	24
<b>Total Ports, quantity, front</b>	6

## Dimensions

<b>Height</b>	27.94 mm   1.1 in
<b>Width</b>	91.44 mm   3.6 in

# 760220418 | 360CM12-4x6-TS

---

**Depth** 109.22 mm | 4.3 in

## Optical Specifications

**Fiber Mode** Singlemode  
**Fiber Type** G.652.D | G.657.A1, TeraSPEED® | OS2  
**Insertion Loss Change, mating** 0.3 dB  
**Insertion Loss Change, temperature** 0.3 dB  
**Insertion Loss, maximum** 1.34 dB

## Environmental Specifications

**Safety Standard** UL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Insertion Loss Change, mating** Maximum insertion loss change after 500 matings  
**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)