## FD3-AB096J1TRKBM3



Enhanced Mini FDH, 96F loaded pole/wall mounted cabinet, SC/APC, preloaded w/ 1x 1:32 PNP splitter, using a 100ft 1x96F Indoor OFNR Ribbon distribution cable assembly and Loose Tube pigtails capable of splicing a 36F feeder

## **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

Product Series FDH 3000

General Specifications

**Access** Front

Cable TypeIndoor - RibbonColorPutty white

**Distribution Cables, quantity** 1

**Distribution Ports, quantity** 96

Fibers per Distribution Cable, quantity 96

Fibers per Feeder Cable, quantity 36

Interface, Input SC

Interface Feature, Input APC

Mounting Pole | Wall Split Ratio Symmetrical

Splitter Slots, quantity 8

**Splitter Type** 1 x 32

Splitter, quantity 1

**Dimensions** 

 Height
 584.2 mm | 23 in

 Width
 330.2 mm | 13 in

 Depth
 203.2 mm | 8 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Mini



## FD3-AB096J1TRKBM3

## Material Specifications

**Finish** Powder coated

Material Type Aluminum

**Environmental Specifications** 

Environmental Space Above ground | Aerial

Qualification Standards Telcordia GR-3123-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

