## FD3-AG360J00GDBP1



FDH 3000 Fiber Distribution Medium Cabinet, 360F, SC/APC, no splitters, single armor loose tube, 100 ft, 12F

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

Product Series FDH 3000

General Specifications

**Access** Front

Cable TypeArmored - Single Loose Tube

**Color** Putty white

Distribution Cables, quantity 3

**Distribution Ports, quantity** 432

Fibers per Feeder Cable, quantity 12

Interface, Input SC

Interface Feature, Input APC

**Mounting** Pad

Splitter Slots, quantity 24

Dimensions

**Height** 1,066.8 mm | 42 in

**Width** 685.8 mm | 27 in

**Depth** 457.2 mm | 18 in

 Cable Length
 30.48 m | 100 ft

**Enclosure Size** Medium

Material Specifications

**Finish** Powder coated

Material Type Aluminum



# FD3-AG360J00GDBP1

#### **Environmental Specifications**

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

