

FD3-AR036J00U00P8



Mini FDH 3000 Fiber Distribution Hub, 72-fiber shell, 36 fibers loaded, SC /APC, distribution pigtails, feeder pigtails

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
Warranty	One year

General Specifications

Access	Front
Cable Type	Pigtails - Loose Tube
Color	Putty white
Distribution Cables, quantity	3
Distribution Ports, quantity	72
Fibers per Distribution Cable, quantity	12
Fibers per Feeder Cable, quantity	8
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole Wall
Splitter Slots, quantity	4

Dimensions

Height	482.6 mm 19 in
Width	330.2 mm 13 in
Depth	203.2 mm 8 in
Enclosure Size	Mini

Material Specifications

Finish	Powder coated
Material Type	Aluminum

FD3-AR036J00U00P8

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted



* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines