

FD3-PA132J00U3420



FDH 3000 Fiber Distribution Hub in a Pedestal, 132F, SC/APC, no-splitters loaded stranded pigtails, 132 splice capacity, 12F feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

Regional Availability	North America
Product Type	Hub in a pedestal
Product Series	FDH 3000

General Specifications

Access	Front Rear
Cable Type	Pigtails - Stranded
Color	Green
Distribution Cables, quantity	12
Distribution Ports, quantity	132
Fibers per Distribution Cable, quantity	12
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Lock Type	Locking bolt
Mounting	Pad
Splice Tray Included, quantity	4
Splice Tray Type Included	36-way, heat shrink
Splicing Capacity, maximum	132
Splitter Slots, quantity	6

Dimensions

Height	889 mm 35 in
---------------	----------------

FD3-PA132J00U3420

Width	292.1 mm 11.5 in
Depth	368.3 mm 14.5 in
Enclosure Size	Small

Material Specifications

Material Type	Steel
----------------------	-------

Environmental Specifications

Environmental Space	Above ground
----------------------------	--------------

Packaging and Weights

Included	Cable clamps (4)
Packaging quantity	1
Packaging Type	Pallet
Weight, net	540 lb 244.94 kg