

# 760237217 | CM12-2X3-LS-ULL



G2 ULL 2x3 Multimode OM4 Conversion Module, (2) MPO-12 unpinned ports rear, (3) MPO-8 pinned front

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber module  |
| <b>Product Brand</b>         | SYSTEMAX ULL  |

## General Specifications

|                                     |                         |
|-------------------------------------|-------------------------|
| <b>Functionality</b>                | Breakout                |
| <b>Adapters, quantity, front</b>    | 3                       |
| <b>Adapters, quantity, rear</b>     | 2                       |
| <b>Color, front</b>                 | Aqua                    |
| <b>Color, rear</b>                  | Aqua                    |
| <b>Data Module Type</b>             | Fiber Conversion Module |
| <b>Interface, front</b>             | MPO                     |
| <b>Interface Feature, front</b>     | Standard                |
| <b>Interface, rear</b>              | MPO                     |
| <b>Interface Feature, rear</b>      | Key up   Unpinned       |
| <b>Polarity</b>                     | Method B Enhanced (ULL) |
| <b>Shuttered</b>                    | No                      |
| <b>Total Fibers, quantity</b>       | 24                      |
| <b>Total Ports, quantity, front</b> | 3                       |

## Dimensions

|               |                    |
|---------------|--------------------|
| <b>Height</b> | 26.42 mm   1.04 in |
| <b>Width</b>  | 96.52 mm   3.8 in  |

# 760237217 | CM12-2X3-LS-ULL

---

**Depth** 117.35 mm | 4.62 in

## Optical Specifications

**Fiber Mode** Multimode  
**Fiber Type** OM4, LazrSPEED® 550  
**Insertion Loss, maximum** 0.4 dB

## Environmental Specifications

**Safety Standard** cUL US 1863

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant  |

