760238838 | DM12-12LC-LS-ULL



G2 ULL Multimode OM4 MPO-12 Distribution Module, 12LC to 1X12f MPOs unpinned, internal shutters

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber moduleProduct BrandSYSTIMAX ULL

Product Series G2

General Specifications

Functionality

Color, front

Color, rear

Interface, front

LC/UPC

Interface, rear

Breakout

Aqua

Gray

LC/UPC

Interface Feature, rear Key up/up | MPO Non-Pinned

Polarity Method B Enhanced (ULL)

Shuttered Yes
Total Fibers, quantity 12

Dimensions

 Height
 26.42 mm | 1.04 in

 Width
 96.52 mm | 3.8 in

 Depth
 117.35 mm | 4.62 in

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED® 550

Insertion Loss, maximum 0.35 dB



760238838 | DM12-12LC-LS-ULL

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.01 kg | 0.022 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

