760234762 | OCM6-SP218S2-72CB1



OCM6 Fiber Optic Splitter Module, Planar, two 1x8 Splitters, singlemode, SC/APC, symmetrical split ratio, butt style, 72 cm pigtails

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

Product Series OCM6

General Specifications

Device Type Standard VAM

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Application For use with BUDI wall boxes

Circuits, quantity 2

Distribution Type1 x 8 splitterInterface, InputSC/APCInterface, OutputSC/APC

Split Ratio Symmetrical

Splitter, quantity 2

Dimensions

 Height
 130 mm | 5.118 in

 Width
 49.8 mm | 1.961 in

 Depth
 16.5 mm | 0.65 in

 Pigtail Length, Input
 0.72 m | 2.362 ft

 Pigtail Length, Output
 0.72 m | 2.362 ft

 Pigtail Diameter
 1.8 mm | 0.071 in

Packaging and Weights



760234762 | OCM6-SP218S2-72CB1

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

