## EG8277-000 | OCM6-SA722NS2-72CB1



OCM6 Fiber Optic Splitter Module, FBT, seven 2x2 Splitters, singlemode, SC/APC output only, symmetrical split ratio, butt style, 72 cm pigtails

#### **Product Classification**

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

**Product Series** OCM6

## General Specifications

**Device Type** Standard VAM

**Functionality** Splitting

**Technology Type** Fused biconic tapered

**Application** For use with BUDI wall boxes

Circuits, quantity 7

Distribution Type2 x 2 splitterInterface, InputStub tailInterface, OutputSC/APC

**Split Ratio** Symmetrical

Splitter, quantity 7

#### Dimensions

 Height
 130 mm | 5.118 in

 Width
 49.8 mm | 1.961 in

 Depth
 16.5 mm | 0.65 in

 Pigtail Length, Input
 2.1 m | 6.89 ft

 Pigtail Length, Output
 2.1 m | 6.89 ft

 Pigtail Diameter
 1.8 mm | 0.071 in

COMMSCOPE°

# EG8277-000 | OCM6-SA722NS2-72CB1

## Packaging and Weights

Packaging quantity

1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

