EH0777-000 | OCM6-SP318S2-18DB1



OCM6 Fiber Optic Splitter Module, Planar, three 1x8 Splitters, singlemode, SC/APC, symmetrical split ratio, butt style, 1.8 m pigtails

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM	
Functionality	Splitting	
Technology Type	Planar lightwave circuit (PLC)	
Application	For use with BUDI wall boxes	
Circuits, quantity	3	
Distribution Type	1 x 8 splitter	
Interface, Input	SC/APC	
Interface, Output	SC/APC	
Split Ratio	Symmetrical	
Splitter, quantity	3	
Dimensions		
DITIETSIONS		
Height	130 mm 5.118 in	
	130 mm 5.118 in 49.8 mm 1.961 in	
Height		
Height Width	49.8 mm 1.961 in	
Height Width Depth	49.8 mm 1.961 in 16.5 mm 0.65 in	

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023



EH0777-000 | OCM6-SP318S2-18DB1

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023

