



OCM5 Fiber Optic Splitter Module, Planar, one 1x32 Splitter, singlemode, SC/APC, symmetrical split ratio, 1.8 m pigtailed

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM5

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Access</b>	Front
<b>Application</b>	For use with FIST cabinets
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 32 splitter
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Interface, Output</b>	SC
<b>Interface Feature, Output</b>	APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	154 mm   6.063 in
<b>Width</b>	16 mm   0.63 in
<b>Depth</b>	142 mm   5.591 in

**Pigtail Length, Input** 1.8 m | 5.906 ft

**Pigtail Length, Output** 1.8 m | 5.906 ft

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

