

760036457 | MODG2-6SCA-SM-PT-B

G2 Modular Cassette with 6 SC APC TeraSPEED® Singlemode Pigtails, Type B

OBSOLETE

Replaced By:

760109587

360G2 Cartridge 6-SCA-SM-GR-PIGTAILS B

360G2 Singlemode Fiber Cassette 6 SC APC with pigtails B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	TeraSPEED®

General Specifications

Adapter Color	Green
Interface, front	SC/APC
Interface, rear	Stranded pigtail
Total Fibers, quantity	6
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Insertion Loss, typical	0.4 dB
Return Loss, minimum	65 dB

Environmental Specifications

760036457 | MODG2-6SCA-SM-PT-B

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

760061374 – TeraSPEED® SC-APC Multiport Shuttered Adapter, Green, Single Pack
AFA-SC06-GR-SHUTTERED