760082495 | RK6-45A



Equipment Rack, 2-Post, 6 in (152 mm) Channel x 7 ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type 2 post rack

General Specifications

Color Black
Rack Type EIA 19 in

Rack Units 45

Rail Mounting Hole #12-24

Dimensions

 Height
 2,133.6 mm | 84 in

 Channel Width
 152.4 mm | 6 in

Width 516.13 mm | 20.32 in

Depth 457.2 mm | 18 in

Dimensional Standards EIA-310-E

Material Specifications

Finish Powder-coated, textured

Material Type Aluminum

Mechanical Specifications

Load Rating453.592 kg | 1000 lbLoad Rating Noteper UL2416 standard

Packaging and Weights

Included Forty #12-24 x 1/2 in mounting screws | Instruction sheet | Twelve 3/8 in split lock

Page 1 of 2



760082495 | RK6-45A

washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base

angles | Two extruded top angles | Two vertical rack rails

Packaging quantity

Packaging Type Flat packed

Weight, net 13.61 kg | 30.005 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant