



Equipment Rack, 4-Post, 29 in (737 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	4 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	52
Rail Mounting Hole	#12-24

Dimensions

Height	2,438.4 mm 96 in
Channel Width	76.2 mm 3 in
Width	518.16 mm 20.4 in
Depth	1,041.4 mm 41 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

Mechanical Specifications

Load Rating	907.185 kg 2000 lb
--------------------	----------------------

Packaging and Weights

Included	Base pan Forty #12-24 x 1/2 in mounting screws Four vertical rack rails Instruction sheet Twenty four 3/8 in split lock washers Twenty four 3/8-16 UNC x 1 in hex head
-----------------	--

760082537 | RK4P52-29A

bolts | Twenty four 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

Packaging quantity	1
Packaging Type	Flat packed
Weight, net	41.28 kg 91.007 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

