

760092015 | RK3-52AM



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) M6 Tapped Rails, Black

OBSOLETE

This product was discontinued on: November 30, 2018

Replaced By:

760090126
RK3-52S

Equipment Rack, 2-Post, 3 in (76 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	52
Rail Mounting Hole	M6

Dimensions

Height	2,438.4 mm 96 in
Channel Width	76.2 mm 3 in
Width	518.16 mm 20.4 in
Depth	381 mm 15 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

760092015 | RK3-52AM

Mechanical Specifications

Static Load Rating 453.6 kg | 1,000.016 lb

Packaging and Weights

Included Four M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

Packaging quantity 1

Packaging Type Flat packed

Weight, net 15.88 kg | 35.009 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system