

760139113 | RK3-58A



Rack, 2-Post, (58U), 3 in (76 mm) Channel x 9 ft (2743 mm) H x 19 in (482.6 mm) W, alum, 12-24 tapped rails, black

OBSOLETE

This product was discontinued on: November 30, 2018

Replaced By:

760082487
RK3-52A

Equipment Rack, 2-Post, 3 in (76 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	58
Rail Mounting Hole	#12-24

Dimensions

Height	2,743.2 mm 108 in
Channel Width	76.2 mm 3 in
Width	515.62 mm 20.3 in
Depth	381 mm 15 in
Dimensional Standards	EIA-310-D

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

760139113 | RK3-58A

Mechanical Specifications

Static Load Rating 453.6 kg | 1,000.016 lb

Packaging and Weights

Included Forty #12-24 x 1/2 in mounting screws | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

Packaging quantity 1

Packaging Type Flat packed

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

