

760245400 | G2-SP-12LCX-RPT



G2 Splice Cassette, 12LC with internal shutters, OM4, with ribbon pigtails

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber cassette with ribbon pigtail |
| Product Series | G2 |

General Specifications

| | |
|-------------------------------|-----------------|
| Color, front | Aqua |
| Interface, front | LC/UPC |
| Interface, rear | Ribbon pigtail |
| Polarity | Pairs, straight |
| Shuttered | Yes |
| Total Fibers, quantity | 12 |

Dimensions

| | |
|---------------|----------------------|
| Height | 26.416 mm 1.04 in |
| Width | 96.52 mm 3.8 in |
| Depth | 165.354 mm 6.51 in |

Material Specifications

| | |
|----------------------------------|----------|
| Alignment Sleeve Material | Zirconia |
|----------------------------------|----------|

Optical Specifications

| | |
|--------------------------------|-----------|
| Fiber Mode | Multimode |
| Fiber Type | OM4 |
| Insertion Loss, maximum | 0.15 dB |

760245400 | G2-SP-12LCX-RPT

Return Loss, minimum 35 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL

Packaging and Weights

Included SMOUV holder | SMOUV splice protection

Packaging quantity 1

Weight, net 0.114 kg | 0.252 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

