



FACT® Fiber Optic Termination/Splice Panel, 48-port, LC/UPC, multimode, with pigtails, right-sided patch cord exit of Panel

- Lightweight, compact and fully configurable with a variety of adapters, splicing and passive optical components
- Cable attachment bracket kits allow secure mounting of different cable types and patch cords to the sides of the FACT panel
- Each FACT panel unit -offering 48 LC connections- can be deployed individually or combined into high-density panels
- Designed for use with the FIST-GR3 optical distribution frame for holding up to 56 FACT panel units

## OBSOLETE

This product was discontinued on: July 31, 2018

### Replaced By:

760240602  
FACT-1ERHPL4A

FACT® Fiber Optic Patch/Splice Panel, gray, 1E high, 48-port, multimode, OM4, loaded with LC/UPC adapters and pigtails, ANT splice tray type, right-hand patch

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Brand</b>	FACT®
<b>Product Series</b>	FACT

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Compatible with FIST-GR3-style frames
<b>Color</b>	Gray
<b>Color, front</b>	Gray
<b>Interface, front</b>	LC
<b>Interface Feature, front</b>	Standard
<b>Patch Cord Routing</b>	Right sided
<b>Rack Type</b>	EIA 19 in   ETSI 600 mm

# EH9089-000 | FACT-GPS-048L5AI-0NN

---

<b>Rack Units</b>	0.7
<b>Shelf Movement</b>	Sliding
<b>Splicing Capacity, maximum</b>	48
<b>Splicing Type</b>	SMOUV
<b>Total Ports, quantity</b>	48

## Dimensions

<b>Height</b>	30.95 mm   1.219 in
<b>Width</b>	524 mm   20.63 in
<b>Depth</b>	283 mm   11.142 in

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-20 °C to +85 °C (-4 °F to +176 °F)

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

