

FIST Oval port seal kit for single fiber loose tube cable

- For sealing two cables having a diameter range of 12-25 mm through the oval outlet port (numbered 1-2) of the closure
- Included plastic sleeve stores the uncut loose buffer tubes between the 2 UMS profiles

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink sealing kit
Product Series	FIST-GC02

General Specifications

Application	For use with FIST-GC02 Fiber closures
Cable Capacity, maximum	1
Color	Black

Dimensions

Single Cable Diameter, maximum	25 mm 0.984 in
Single Cable Diameter, minimum	12 mm 0.472 in

Packaging and Weights

Included	Cable termination brackets Dummy plugs Multi-out gel seal
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

