



PEDCAP Copper Closure, butt, unpressurized, heat shrink, 250 mm joint length, for up to 4 cables

- One piece end cap with heat-shrinkable outlet for sealing onto the cables
- Provides an excellent environmental and mechanical seal for telephone splices in the distribution network
- Suitable for use as an overhead, underground or pedestal joint closure in both new construction and maintenance applications

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Unpressurized heat shrink closure
<b>Product Series</b>	PEDCAP

## General Specifications

<b>Application</b>	For use with Polyethylene and metal jacketed cables
<b>Cable Capacity, maximum</b>	4
<b>Cable Sealing Type</b>	Hotmelt adhesive
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Pedestal
<b>Splicing Capacity, maximum</b>	200

## Dimensions

<b>Length</b>	360 mm   14.173 in
<b>Single Cable Diameter, maximum</b>	60 mm   2.362 in
<b>Single Cable Diameter, minimum</b>	25 mm   0.984 in
<b>Splice Bundle Diameter, maximum</b>	84 mm   3.307 in
<b>Sheath Opening, nominal</b>	250 mm   9.843 in

## Material Specifications

# 247386-000 | PED-CAP-R-4S-INT

---

**Material Type** Polyolefin

## Environmental Specifications

**Environmental Space** Aerial | Buried

## Packaging and Weights

**Included** Aluminum closing strip | Aluminum foil | Cleaning tissues | Desiccant | Tie wraps

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](https://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

