# 284765-000 | GELSNAP-C-18/5-180-INT

#### GELSNAP Copper Closure, unpressurized, gel sealed, butt/in-line, for up to 30 pair splices

- Prevents water ingress by use of non-flowing gel under permanent compression
- Robust and reliable under a wide variety of environmental conditions
- Butt, in-line, and branch configurations with many connector types are possible

#### Product Classification

Regional Availability	Asia   EMEA   North America
Product Type	Gel filled closure
Product Series	GELSNAP
General Specifications	
Cable Sealing Type	Gel filled
Closure Style	In-line   Single-ended
Color	Black
Splicing Capacity, maximum	30
Dimensions	
Height	33 mm   1.299 in
Width	80 mm   3.15 in
Length	335 mm   13.189 in
Single Cable Diameter, maximum	18 mm   0.709 in
Single Cable Diameter, minimum	5 mm   0.197 in
Sheath Opening, nominal	180 mm   7.087 in


## Dimension Drawing

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 27, 2024



# 284765-000 | GELSNAP-C-18/5-180-INT



## Environmental Specifications

 Environmental Space
 Aerial | Buried

 Packaging and Weights
 Gel compression springs | Gel-filled half-shells | Installation instruction | Strain relief accessories | Tie wraps

 Packaging quantity
 1

 Packaging Type
 Bag | Carton

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
TL 9000:2016 (R6)	Compliant to this quality management practice
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 27, 2024

