

475557-000 | XAGA1000-E3-KIT-M478

XAGA® 1000 Copper Closure, pressurized, heat shrink, 37 inch sheath opening, 7.8 inch splice bundle diameter



- Full range of closures to suit all copper cable sizes
- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	Latin America North America
Product Type	Pressurized heat shrink closure
Product Brand	XAGA®
Product Series	XAGA 1000

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Branch-off Clip	To be ordered separately
Cable Capacity, maximum	4
Cable Sealing Type	Hotmelt adhesive
Closure Style	In-line
Color	Black
Mounting	Duct Manhole
Splice Protection Type	Metal canister with valve

Dimensions

Single Cable Diameter, minimum	66.04 mm 2.6 in
Splice Bundle Diameter, maximum	198.12 mm 7.8 in
Sheath Opening, nominal	939.8 mm 37 in

Dimension Drawing



Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

