619625-000 | GELSNAP-A-10/5-80-INT



GELSNAP Copper Closure, unpressurized, gel sealed, butt, for up to 3 pair splices

- Prevents water ingress by use of non-flowing gel under permanent compression
- Robust and reliable under a wide variety of environmental conditions
- Butt, in-line, and branch configurations with many connector types are possible

Product Classification

Regional Availability EMEA

Product Type Gel filled closure

Product Series GELSNAP

General Specifications

Cable Sealing Type Gel filled

Closure Style Single-ended

Color Black

Splicing Capacity, maximum 3

Dimensions

 Height
 33 mm | 1.299 in

 Width
 64 mm | 2.52 in

 Length
 155 mm | 6.102 in

 Single Cable Diameter, maximum
 10 mm | 0.394 in


 Single Cable Diameter, minimum
 5 mm | 0.197 in

 Sheath Opening, nominal
 80 mm | 3.15 in

Dimension Drawing



619625-000 | GELSNAP-A-10/5-80-INT



Environmental Specifications

Environmental Space Aerial | Buried

Packaging and Weights

Included Gel compression springs | Gel-filled half-shells | Installation instruction | Strain relief

accessories | Tie wraps

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
TL 9000:2016 (R6)	Compliant to this quality management practice
UK-ROHS	Compliant

