

760157800 | OVRHDRACK



3 in (76 mm) Channel x 9.4 in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (4U) 3/8 Sq Punch, Black

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Mini-rack, overhead |

General Specifications

| | |
|-------------------|-----------|
| Color | Black |
| Rack Type | EIA 19 in |
| Rack Units | 4 |

Dimensions

| | |
|------------------------------|---------------------|
| Height | 238.76 mm 9.4 in |
| Channel Width | 76.2 mm 3 in |
| Width | 500.38 mm 19.7 in |
| Depth | 76.2 mm 3 in |
| Dimensional Standards | EIA-310-E |

Material Specifications

| | |
|----------------------|-------------------------|
| Finish | Powder-coated, textured |
| Material Type | Steel |

Mechanical Specifications

| | |
|--------------------|-------------------|
| Load Rating | 27.216 kg 60 lb |
|--------------------|-------------------|

Packaging and Weights

| | |
|-----------------|--|
| Included | Instruction sheet Six 5/16-18 hex nuts Six 5/16-18 hex screws Sixteen M6 cage nuts Sixteen M6 mounting screws Two flat washers Two ladder clamp brackets Two mounting brackets |
|-----------------|--|

760157800 | OVRHDRACK

Packaging quantity 1
Packaging Type Assembled

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

