



SCIL-A Fiber splice closure, in-line, with 4 gel cable sealing kits, 1 pre-installed 24-splice tray and SMOUV protectors, no ground feedthrough lug, no air valve

- Leverages proven FOSC™ fiber management system, with multiple splice tray options
- Removeable cover allows unrestricted access to cable termination and splice area for easier installation
- Cable termination and retention system fits any cable type from traditional loose tube buffered to small micro-sheath cables

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	In-line, rectangular fiber closure
Product Brand	SCIL™
Product Series	SCIL-A

General Specifications

Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports Quantity, total	2 round ports + 8 multi-out ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Side latch
Closure Style	In-line
Color	Black
Flash Test Valve	None
Ground Feed-through	None
Mounting	Facade Wall
Network Area Type	Drop
Splice Tray Included, quantity	1
Splice Tray Type Included	24-way, heat shrink
Splicing Capacity, Single Fusion, maximum	48
Splicing Capacity, Single Splice, 12 fibers, maximum	48
Splicing Type, Supported	Single fusion

760238014 | SCIL-A-S24

Dimensions

Height	70 mm 2.756 in
Width	100 mm 3.937 in
Length	250 mm 9.843 in
Main Cable Diameter, maximum	11 mm 0.433 in

Ordering Tree

SCIL-A-¹___

Tray type

1	S24	Splice tray for 24 splices
	S48	Splice tray for 48 splices

SMOUV splice protectors included

Material Specifications

Material Type Rugged polymer

Environmental Specifications

Environmental Space Above ground | Below ground

Qualification Standards IEC 60529, IP68 + 2 m waterhead

Packaging and Weights

Included SMOUV splice protectors (24)

Packaging quantity 1

Packaging Type Box | Carton

Weight, net 1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant

UK-ROHS

Compliant

