



SCIL-A Fiber splice closure, in-line, with 4 gel cable sealing kits, 1 pre-installed 48-splice tray and SMOUV protectors, no ground feedthrough lug, no air valve

- Leverages proven FOSC™ fiber management system, with multiple splice tray options
- Removeable cover allows unrestricted access to cable termination and splice area for easier installation
- Cable termination and retention system fits any cable type from traditional loose tube buffered to small micro-sheath cables

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	In-line, rectangular fiber closure
<b>Product Brand</b>	SCIL™
<b>Product Series</b>	SCIL-A

## General Specifications

<b>Cable Entry Drop Port Style</b>	Round
<b>Cable Entry Main Port Style</b>	Round
<b>Cable Ports Quantity, total</b>	2 round ports + 8 multi-out ports
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Side latch
<b>Closure Style</b>	In-line
<b>Color</b>	Black
<b>Flash Test Valve</b>	None
<b>Ground Feed-through</b>	None
<b>Mounting</b>	Facade   Wall
<b>Network Area Type</b>	Drop
<b>Splice Tray Included, quantity</b>	1
<b>Splice Tray Type Included</b>	48-way, heat shrink
<b>Splicing Capacity, Single Fusion, maximum</b>	48
<b>Splicing Capacity, Single Splice, 12 fibers, maximum</b>	48
<b>Splicing Type, Supported</b>	Single fusion

# 760238015 | SCIL-A-S48

## Dimensions

<b>Height</b>	70 mm   2.756 in
<b>Width</b>	100 mm   3.937 in
<b>Length</b>	250 mm   9.843 in
<b>Main Cable Diameter, maximum</b>	11 mm   0.433 in

## Ordering Tree

SCIL-A-<sup>1</sup>\_\_\_

Tray type

1	S24	Splice tray for 24 splices
	S48	Splice tray for 48 splices

SMOUV splice protectors included

## Material Specifications

<b>Material Type</b>	Rugged polymer
----------------------	----------------

## Environmental Specifications

<b>Environmental Space</b>	Above ground   Below ground
<b>Qualification Standards</b>	IEC 60529, IP68 + 2 m waterhead

## Packaging and Weights

<b>Included</b>	SMOUV splice protectors (48)
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Weight, net</b>	1 kg   2.205 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant

UK-ROHS

Compliant

