760242108 | PNL-CS-12LCV-PT



Product Classification

Standard Density (SD) Splicing cassette 12LC OM5, 900#m

PIOUULI CIASSIIICALION	
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
General Specifications	
Adapter Color	Lime green
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	12
Total Ports, quantity, front	6
Dimensions	
Height	28.956 mm 1.14 in
Width	104.648 mm 4.12 in
Depth	165.354 mm 6.51 in
Pigtail Length	1.5 m 4.921 ft
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED® wideband
Insertion Loss, typical	0.3 dB
Environmental Specifications	
Safety Standard	UL

Packaging and Weights

Packaging quantity

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

1



Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

