760242109 | PNL-CS-24LCV-PT



Standard Density (SD) splicing cassette 24LC OM5, 900#m

Product Classification	
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
General Specifications	
Adapter Color	Lime green
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	24
Total Ports, quantity, front	12
Dimensions	
Height	28.956 mm 1.14 in
Width	104.648 mm 4.12 in
Depth	165.354 mm 6.51 in
Pigtail Length	1.5 m 4.921 ft
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED® wideband
Insertion Loss, typical	0.3 dB
Environmental Specifications	
Safety Standard	UL

Packaging and Weights

Packaging quantity

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

1



Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

