



CHD ULL Singlemode Splice Cassette, 12LC, with dust plugs and ribbon pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with ribbon pigtail
Product Brand	SYSTIMAX ULL
Product Series	CHD

General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Ribbon pigtail
Polarity	Method A Pairs, straight
Shuttered	No
Total Fibers, quantity	12

Dimensions

Height	12.446 mm 0.49 in
Width	83.82 mm 3.3 in
Depth	184.658 mm 7.27 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

760244825 | CHD-SP-12LC-SMR-AS-ULL

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Included Mass Fusion Splice Protection Sleeves

Packaging quantity 1

Weight, net 0.095 kg | 0.21 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
RCM	Compliant to electrical safety & telecommunications requirements
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack